

# Mold List

## O-ring

|        |           |                  |
|--------|-----------|------------------|
| O-ring | AS568-004 | 1.78×1.78×5.34   |
| O-ring | AS568-005 | 1.78×2.57×6.13   |
| O-ring | AS568-006 | 1.78×2.9×6.46    |
| O-ring | AS568-007 | 1.78×3.68×7.24   |
| O-ring | AS568-008 | 1.78×4.47×8.03   |
| O-ring | AS568-009 | 1.78×5.28×8.84   |
| O-ring | AS568-010 | 1.78×6.07×9.63   |
| O-ring | AS568-011 | 1.78×7.65×11.21  |
| O-ring | AS568-012 | 1.78×9.25×12.81  |
| O-ring | AS568-013 | 1.78×10.82×14.38 |
| O-ring | AS568-014 | 1.78×12.42×15.98 |
| O-ring | AS568-015 | 1.78×14×17.56    |
| O-ring | AS568-016 | 1.78×15.6×19.16  |
| O-ring | AS568-017 | 1.78×17.17×20.73 |
| O-ring | AS568-018 | 1.78×18.77×22.33 |
| O-ring | AS568-019 | 1.78×20.35×23.91 |
| O-ring | AS568-020 | 1.78×21.95×25.51 |
| O-ring | AS568-021 | 1.78×23.52×27.08 |
| O-ring | AS568-022 | 1.78×25.12×28.68 |
| O-ring | AS568-023 | 1.78×26.7×30.26  |
| O-ring | AS568-024 | 1.78×28.3×31.86  |
| O-ring | AS568-025 | 1.78×29.87×33.43 |
| O-ring | AS568-105 | 2.62×3.63×8.87   |
| O-ring | AS568-106 | 2.62×4.42×9.66   |
| O-ring | AS568-107 | 2.62×5.23×10.47  |
| O-ring | AS568-108 | 2.62×6.02×11.26  |
| O-ring | AS568-109 | 2.62×7.59×12.83  |
| O-ring | AS568-110 | 2.62×9.19×14.43  |
| O-ring | AS568-112 | 2.62×12.37×17.61 |
| O-ring | AS568-113 | 2.62×13.94×19.18 |
| O-ring | AS568-114 | 2.62×15.54×20.78 |
| O-ring | AS568-115 | 2.62×17.12×22.36 |
| O-ring | AS568-116 | 2.62×18.72×23.96 |
| O-ring | AS568-117 | 2.62×20.29×25.53 |
| O-ring | AS568-118 | 2.62×21.89×27.13 |
| O-ring | AS568-120 | 2.62×25.07×30.31 |

|        |           |                  |
|--------|-----------|------------------|
| O-ring | AS568-130 | 2.62×40.94×46.18 |
| O-ring | AS568-207 | 3.53×13.87×20.93 |
| O-ring | AS568-208 | 3.53×15.47×22.53 |
| O-ring | AS568-209 | 3.53×17.04×24.1  |
| O-ring | AS568-210 | 3.53×18.64×25.7  |
| O-ring | AS568-236 | 3.53×82.14×89.2  |
| O-ring | AS568-803 | 1.78×6.35×9.91   |
| O-ring | P-3       | 1.9×2.8×6.6      |
| O-ring | P-4       | 1.9×3.8×7.6      |
| O-ring | P-5       | 1.9×4.8×8.6      |
| O-ring | P-6       | 1.9×5.8×9.6      |
| O-ring | P-7       | 1.9×6.8×10.6     |
| O-ring | P-8       | 1.9×7.8×11.6     |
| O-ring | P-9       | 1.9×8.8×12.6     |
| O-ring | P-10      | 1.9×9.8×13.6     |
| O-ring | P-10A     | 2.4×9.8×14.6     |
| O-ring | P-12      | 2.4×11.8×16.6    |
| O-ring | P-14      | 2.4×13.8×18.6    |
| O-ring | P-15      | 2.4×14.8×19.6    |
| O-ring | P-16      | 2.4×15.8×20.6    |
| O-ring | P-18      | 2.4×17.8×22.6    |
| O-ring | P-20      | 2.4×19.8×24.6    |
| O-ring | P-21      | 2.4×20.8×25.621  |
| O-ring | P-22      | 2.4×21.8×26.6    |
| O-ring | P-24      | 3.5×23.7×30.7    |
| O-ring | P-26      | 3.5×25.7×32.7    |
| O-ring | P-32      | 3.5×31.7×38.7    |
| O-ring | P-39      | 3.5×38.7×45.7    |
| O-ring | P-40      | 3.5×39.7×46.7    |
| O-ring | P-85      | 5.7×84.6×96      |
| O-ring | G-35      | 3.1×34.4×40.6    |
| O-ring | G-45      | 3.1×44.4×50.6    |
| O-ring | G-95      | 3.1×94.4×100.6   |
| O-ring | S-12      | 1.5×11.5×14.5    |
| O-ring | S-18      | 1.5×17.5×20.5    |



**Takaishi Industry Co.,Ltd. (Osaka Japan)**

URL ▶ <http://www.takaishi-ind.co.jp>

E-mail ▶ [inquiry@takaishi-ind.co.jp](mailto:inquiry@takaishi-ind.co.jp)